




Connection
S Y S T E M S

Flexisieve

Data Sheet





Top View



Flexisieve 200



Flexisieve 380 on trolley



Flexisieve 350 & Magnetic Separator on trolley

Flexisieve In-Line Sieving

The Flexisieve In-Line sieve has been developed by our sister company Pharmatech to allow fixed mounting into a pipe line to ensure completely contained safety sieving.

Flexisieve Features

- Rugged all stainless steel construction
- Product contact parts 316 stainless steel and silicone rubber
- Quick changeover between batches & interchangeable heads
- High throughput
- Low noise
- Low maintenance
- GMP correct design
- CE marked
- ATEX Rated versions available
- Drive unit can be orientated at any angle to the sieve unit head
- Wide range of screen sizes
- Free standing versions
- Clamped to adjacent equipment using our special clamps
- Head completely detachable from drive unit to allow removal from pipeline for cleaning.

Materials

One piece heavy duty, silicone liner made from FDA compliant, white silicone rubber. Liner conforms to CFR(FDA) standard 177.2600

Technical

Typical through put rate using a 500mm (30#) sieve plate with lactose:

Flexisieve 200mm - 750kg per hour

Flexisieve 350mm - 2000kg per hour

For further technical information see our Flexisieve brochure.

Connection Systems

4- 5 Forge Mills Park, Station Road,
Coleshill, Warwickshire. U.K. B46 1JH

Tel: +44 (0)1675 469 030

www.connectionsystems.co.uk

Connection Systems is a division of Terriva Ltd